

ACC020

Non-fused 2-wire test lead set

PRODUCT DATA SHEET

ACC020

- G7 Precision high quality multistranded test leads
- Double insulated with a different colour for each layer of insulation
- Instrument conn: Right angled 4mm connector
- Probe conn: 4mm connector
- Probes: 1 x red, 1 x black
- Croc Clips: 1 x red, 1 x black
- For: Ins. / cont. testers, clamp meters, DMMs and testing accessories




SPECIFICATION

Standard	BSEN 61010-031 CAT III 600V
Test lead length	1030 mm
Connectors	4 mm
Strands	176 strands 1.00mm ² total csa
O.D	3.8mm nominal outer diameter

PRODUCT INFO

- 72 x 55 x 130 Boxed (WxDxH mm)
- 0.19kg Weight
- EAN 5060084080058
- Made in China

G7 test criteria



kewtechcorp.com
0345 646 1404
sales@kewtechcorp.com