



Trust Nado II Multi-device Bluetooth® Keyboard - Black US

Compact, multi-device wireless keyboard so you can switch between up to 3 devices at once

Article number: 25730
Barcode: 8713439257304
GTIN: 08713439257304

Core content

Brand	Trust
Product type	Multi-device Bluetooth® Keyboard
Colour	Black
Keyboard layout	QWERTY
Keyboard country code	US
Key features	- Connect with and switch between up to 3 Bluetooth® devices via the easy-switch Fn key combo - Multi-OS support (Windows, iOS, iPadOS, MacOS, Android) - 10m wireless range offers additional freedom of movement - Built-in rechargeable battery – up to 3 months battery life - Compact size with low-profile scissor keys so you can work quietly without disturbing others - Included USB-A-C charge cable to keep on working whilst charging - On-off switch so you can preserve the battery when not in use - 13 multimedia keys for a compact yet full-sized experience
Package contents	- Wireless keyboard - Charge cable - User guide
System requirements	- Windows 10 or 11 - macOS 13, 14 or 15* - iOS 16, 17 or 18* - Android 12, 13, 14 or 15* - Bluetooth connection - USB-A port for charging - *Compatibility office and media function keys may vary between OS

Marketing

Extended retailer text

Specifications

Plastic material	ABS
Total weight	290 g
Weight of main unit	280 g
Height of main product (in mm)	7 mm
Width of main product (in mm)	285 mm
Depth of main product (in mm)	120 mm
Switch Technology	Scissor
Spill-proof	No
Wrist support	No
Keyboard design	Mini
Keypress lifetime	50 M
Fn media keys	Yes
Connection type	Wireless
Connector type	USB-C USB-A
Bluetooth	Yes
Compatible software platforms	Windows MacOS iOS Android

Main image



25730_pictures_product_visual_1.tif

ImageWidth: 5.000 px
ImageHeight: 5.000 px
ImageResolution: 300 dpi

Additional Product Images



25730_pictures_product_top_1.tif

ImageWidth: 5.000 px
ImageHeight: 5.000 px
ImageResolution: 300 dpi



25730_pictures_product_side_1.tif

ImageWidth: 5.000 px
ImageHeight: 5.000 px
ImageResolution: 300 dpi



25730_pictures_product_garan_1.tif

ImageWidth: 7.600 px
ImageHeight: 8.530 px
ImageResolution: 300 dpi

Product Pictorials



25730_EN_pictures_product_pictorial_1.tif

ImageWidth: 4.000 px
ImageHeight: 4.000 px
ImageResolution: 300 dpi



25730_EN_pictures_product_pictorial_2.tif

ImageWidth: 4.000 px
ImageHeight: 4.000 px
ImageResolution: 300 dpi



25730_EN_pictures_product_pictorial_3.tif

ImageWidth: 4.000 px
ImageHeight: 4.000 px
ImageResolution: 300 dpi



25730_EN_pictures_product_pictorial_4.tif

ImageWidth: 4.000 px
ImageHeight: 4.000 px
ImageResolution: 300 dpi



25730_EN_pictures_product_pictorial_5.tif

ImageWidth: 4.000 px
ImageHeight: 4.000 px
ImageResolution: 300 dpi

Lifestyle Images



25730_pictures_lifestyle_visual_1.jpg

ImageWidth: 11.648 px
ImageHeight: 8.736 px
ImageResolution: 300 dpi



25730_pictures_productinuse_visual_1.jpg

ImageWidth: 11.648 px
ImageHeight: 8.736 px
ImageResolution: 300 dpi



25730_pictures_productinuse_visual_2.jpg

ImageWidth: 11.648 px
ImageHeight: 8.736 px
ImageResolution: 300 dpi



25730_pictures_productinuse_visual_3.jpg

ImageWidth: 11.269 px
ImageHeight: 8.372 px
ImageResolution: 300 dpi

Package Images



25730_pictures_package_visual_1.tif
ImageWidth: 5.000 px
ImageHeight: 5.000 px
ImageResolution: 300 dpi



25730_pictures_package_front_1.tif
ImageWidth: 3.495 px
ImageHeight: 1.481 px
ImageResolution: 300 dpi