

Standalone 1 to 5 USB Thumb Drive Duplicator and Eraser, Multiple USB Flash Drive Copier, System and File and Whole-Drive Copy at 1.5 GB/min, Single and 3-Pass Erase, LCD Display - TAA

**Product ID:** USBDUP15



The USBDUP15 OnetoFive USB flash drive duplicator and eraser lets you quickly clone up to five backups of a single USB flash drive, or securely erase up to five flash drives, without connecting to a host computer.

Featuring a compact lightweight design that you can carry anywhere, and standalone operation that does not require a host computer, the flash drive duplicator and eraser has a small desktop footprint and is great for travel. Perfect for software and marketing content distribution in the office or on-the-go.

With an easy-to-read LCD display and intuitive four button menu operation, the USBDUP15 ensures hassle-free setup and control. The menu gives you push-button access to many value-added features that ensure simple task management such as: Capacity & Speed Check, Copy & Compare, Asynchronous Copy, and many more. It also provides numerous advanced setup options for experienced users.

This versatile device is both hard drive cloner and eraser in one, and offers two duplication modes (File & System Copy / Whole Copy) with up to 1.5GB/m at Whole Copy mode. It offers three erase modes (Quick Erase / Full Erase / DoD Erase) giving you the freedom to choose the best solution for your application.

## Certifications, Reports and Compatibility



## Applications

- Software and operating system updating and distributions
- Marketing collateral copying and distribution
- Rich media coping and distributions
- Quickly backup USB flash drives without a host computer
- Create exact copies of a USB flash drive in law enforcement and forensic investigations
- Thoroughly erase data from a flash drive, for added data security and peace of mind
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives

## Features

- **DUPLICATE & ERASE USB DRIVES:** Standalone 1 to 5 USB drive duplicator / cloner / sanitizer; Ideal for technicians and IT Pros to manage multiple USB boot drives, wipe USB drives, or quickly share data between teams; No Computer required
- **DRIVE COMPATIBILITY:** Supports cloning/duplication and erasing of USB 3.0/2.0 flash media thumb drives and USB External Storage (External USB device(s) may require its own power source connecting to outlets); Firmware is upgradeable
- **DUPLICATION AND ERASE MODES:** 1.5 GB/min System & File Copy (FAT16/32, NTFS, Linux ext2, ext3, ext4 formats), whole-drive Sector-by-Sector Copy (all file formats), Quick Erase, Single-Pass & 3-Pass Overwrite (DoD/NIST SP 800-88 Rev 1 Clear); TAA Compliant
- **LCD MENU DISPLAY:** Use push button interface to monitor drive info, read & write performance, and scan drive for errors and bad sectors; Select Copy & Compare to verify your cloned drives with source when complete; Green/Red LEDs for activity/errors
- **ASYNCHRONOUS COPY MODE:** Quickly copy to multiple USB thumb drives using Asynchronous Copy mode w/ 64 MB internal memory; Source content must be under 64 MB; Remove your finished drive and insert a new drive to start copying without interruptions

---

### General

|          |              |
|----------|--------------|
| UPC      | 065030856508 |
| Warranty | 2 Years      |

---

### Special Notes / Requirements

|                               |                                                                                                                                                                                                                                             |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| System and Cable Requirements | For duplication, the destination drives must be of equal or greater capacity than the source drive.<br><br>For erasing, only the destination ports are active, the source port cannot be used. This helps to prevent erasing a source drive |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

accidentally.

Supports copying/cloning/erasing to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure (sold separately) if supported by the storage media

---

#### Power

|                     |                     |
|---------------------|---------------------|
| Power Source        | AC Adapter Included |
| Input Voltage       | 100 - 240 AC        |
| Output Voltage      | 12V DC              |
| Output Current      | 3                   |
| Center Tip Polarity | Positive            |
| Plug Type           | M                   |
| Power Consumption   | 36                  |

---

#### Physical & Environmental

|                       |                         |
|-----------------------|-------------------------|
| Color                 | Black                   |
| Material              | Plastic                 |
| Product Length        | 6.6 in [16.7 cm]        |
| Product Width         | 4.7 in [12 cm]          |
| Product Height        | 1.0 in [25 mm]          |
| Weight of Product     | 11.2 oz [318 g]         |
| Operating Temperature | 5C ~ 45C (41F ~ 113F)   |
| Storage Temperature   | -20C ~ 85C (-4F ~ 185F) |
| Humidity              | 5% ~ 95% RH             |

---

#### Performance

|                    |                                                   |
|--------------------|---------------------------------------------------|
| Buffer Size        | 64 MB                                             |
| Max Drive Capacity | 2TB                                               |
| Duplication Modes  | System and File<br>Sector by Sector (Whole Drive) |

|                   |                                                 |
|-------------------|-------------------------------------------------|
| Duplication Speed | 1.5GBpm                                         |
| Erase Modes       | Quick Erase                                     |
|                   | 1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear) |
|                   | 3-Pass Overwrite                                |
| MTBF              | 176,549 hours                                   |

#### Hardware

|                        |                                      |
|------------------------|--------------------------------------|
| Bus Type               | USB 2.0                              |
| Number of Drives       | 6                                    |
| Compatible Drive Types | USB Flash Drive                      |
| Drive Installation     | Removable                            |
| LED Indicators         | 5 - Green (Activity/Successful Copy) |
|                        | 5 - Red (Error)                      |

#### Packaging & In-the-Box

|                           |                                                                                                                                                                               |
|---------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Included in Package       | 1 - Duplicator                                                                                                                                                                |
|                           | 1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand |
|                           | 1 - Instruction Manual                                                                                                                                                        |
| Package Width             | 9.0 in [22.9 cm]                                                                                                                                                              |
| Package Depth             | 7.0 in [17.7 cm]                                                                                                                                                              |
| Package Height            | 3.3 in [83 mm]                                                                                                                                                                |
| Shipping (Package) Weight | 25.2 oz [714 g]                                                                                                                                                               |

#### Connector(s)

|                        |                       |
|------------------------|-----------------------|
| Connector 1 (Quantity) | 6                     |
| Connector 1            | USB-A (480Mbps, 2.5W) |

*\*Product appearance and specifications are subject to change without notice.*