

2 Port Professional USB KVM Switch Kit with Cables - TAA

Product ID: SV231USBGB




The SV231USBGB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of 2 computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM includes 2 USB KVM cables, for a complete out-of-the-box solution saving you time and money. An integrated 3 port USB hub allows you to share USB peripherals between computers as though they were connected directly. A compact form factor and rear-port connections minimizes disruption to your workspace.

This OS independent KVM supports resolutions up to 1920x1440, and provides a smooth operating experience in mixed (Windows/Mac/Linux) environments.

Certifications, Reports and Compatibility



Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required

General

UPC	065030806039
Package Quantity	1
Warranty	3 Years

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2
Center Tip Polarity	Positive
Plug Type	N
Power Consumption	10

Physical & Environmental

Color	Black
Material	Steel
Product Length	4.9 in [12.4 cm]
Product Width	2.8 in [70.0 mm]
Product Height	1.6 in [40.0 mm]

Product Depth	2.8 in [70 mm]
Weight of Product	14.9 oz [421.0 g]

Performance

Maximum Cable Length	16.4 ft [5 m]
IP Control	No
Hot-Key Selection	No
Port Selection Support	Push Button
On-Screen Display	No
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1
MTBF	111000 hours
DVI Support	No
Maximum Analog Resolutions	1920x1440

Hardware

U Height	1U
Audio	No
Number of KVM Ports	2
Supported Platforms	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Cascadable	No

Packaging & In-the-Box

Included in Package	1 - 2 Port KVM Switch
	2 - 6ft(1.83m) KVM Cables
	1 - Universal power adapter (EU/UK)
	1 - User Manual
Package Width	7.2 in [18.3 cm]
Package Depth	9.3 in [23.5 cm]
Package Height	3.6 in [92 mm]
Shipping (Package) Weight	2.6 lb [1.2 kg]

Connector(s)

Host Connector 1 (Quantity)	2
Host Connector 1	VGA
Host Connector 2 (Quantity)	2
Host Connector 2	USB-B (480Mbps, 2.5W)
Connector 1 (Quantity)	1
Connector 1	VGA
Connector 2 (Quantity)	3
Connector 2	USB-A (480Mbps, 2.5W)

****Product appearance and specifications are subject to change without notice.***