

Technical data sheet

Article number:
151-01144

CC11

Product Group	Connector Clips for Oval Holes
Product Family	With FirTree
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
CE Certification	No
Fixation Method	Fir Tree for oval holes
Flammability	UL 94 HB
for Hole Ø (FH)	9.0 x 16.0 mm, 9.0 x 17.0 mm
Height (H)	20.6 mm
Length (L)	30.0 mm
Operating Temperature	-40 °C to +105 °C
Package Content	5000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 6.5 mm
Panel Thickness max.	6.5 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Variant	9.0 x 17.0 mm 9.0 x 16.0 mm
Width (W)	18.2 mm

