

Technical data sheet

Article number:
151-01033

CCOVAL6

Product Group	Connector Clips for Oval Holes
Product Family	With FirTree
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
CE Certification	No
Fixation Method	Fir Tree for oval holes
Flammability	UL 94 HB
for Hole Ø (FH)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Height (H)	15.2 mm
Length (L)	29.34 mm
Length (L2)	13.4 mm
Operating Temperature	-40 °C to +105 °C
Package Content	1000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 3.0 mm
Panel Thickness max.	3.0 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Variant	6.2 x 12.2 mm 6.5 x 12.5 mm 6.5 x 13.0 mm 7.0 x 12.0 mm
Width (W)	17.6 mm

