

Technical data sheet

Article number:
151-02177

BCATC4

Material	Polyphenylene Sulfide (PPS)
Colour	Silver (SR)
CE Certification	No
Fixation Method	arrowhead
for Hole Ø (FH)	11.7 - 13.0 mm
Height (H)	30.94 mm
Length (L)	75.0 mm
Operating Temperature	-40 °C to +150 °C
Package Content	2000 pcs.
Package Content packed in	pack
Panel Thickness	13.5 - 15.0 mm
Panel Thickness max.	15.0 mm
Panel Thickness min.	13.5 mm
ROHS compliant	Yes
UV-Stabilised	No
Width (W)	11.43 mm

RoHS 