

Technical data sheet

Article number:
151-04320

IBBCLPSLR1

Product Group	Solar I-Beam Clips
Product Family	Effectively routes PV cables
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Bundle Ø max.	50.8 mm
Bundle Ø min.	48.76 mm
CE Certification	No
Fixation Method	Edge Clip
Flammability	UL 94 HB
Height (H)	115.0 mm
Length (L)	21.0 mm
Length (L2)	12.2 mm
Operating Temperature	-40 °C to +110 °C
Package Content	250 pcs.
Package Content packed in	pack
Panel Thickness	3.3 - 12.7 mm
Panel Thickness max.	12.7 mm
Panel Thickness min.	3.3 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	119.8 mm

RoHS 