

Technical data sheet

Article number:
133-03800

TEC48

Product Group	Bundling clips with edge clips
Product Family	for panel thicknesses of 1.0 - 4.0 mm
Material	Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS), Metal (MET)
Colour	Cream (CM)
Bundle Ø max.	7.8 mm
CE Certification	No
Fixation Method	Edge Clip
Height (H)	7.5 mm
Length (L)	15.1 mm
Length (L2)	36.2 mm
Operating Temperature	-40 °C to +105 °C
Package Content	4000 pcs.
Package Content packed in	pack
Panel Thickness	0.8 - 2.0 mm
Panel Thickness max.	2.0 mm
Panel Thickness min.	0.8 mm
ROHS compliant	Yes
UV-Stabilised	No
Width (W)	9.9 mm

RoHS 