

Technical data sheet

Article number:
133-01497

SOC14FT6

Material	Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS)
Colour	Natural (NA)
CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	6.1 - 6.9 mm
Length (L)	45.0 mm
Operating Temperature	-40 °C to +105 °C
Package Content	2000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 6.0 mm
Panel Thickness max.	6.0 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	No

RoHS 