

Technical data sheet

Article number:
151-14303

PC15FT7

Product Family	PC-Series with Firtree
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Bundle Ø max.	15.7 mm
CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	6.4 - 6.8 mm
Height (H)	38.1 mm
Length (L)	15.75 mm
Operating Temperature	-40 °C to +105 °C
Package Content	1000 pcs.
Package Content packed in	pack
Panel Thickness	1.0 - 6.0 mm
Panel Thickness max.	6.0 mm
Panel Thickness min.	1.0 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	21.6 mm

