

Technical data sheet

Article number:
151-01829

MOC26FTOVAL

Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Bundle Ø max.	29.0 mm
Bundle Ø min.	23.0 mm
CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Height (H)	58.1 mm
Length (L)	34.5 mm
Operating Temperature	-40 °C to +105 °C
Package Content	1000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 6.75 mm
Panel Thickness max.	6.75 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	Yes

HF ✓

RoHS ✓