

Technical data sheet

Article number:
151-04351

ROC18.5-22.5FT6.5

Product Group	Ratchet O-Clamp
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Bundle Ø max.	22.5 mm
Bundle Ø min.	18.5 mm
CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	6.1 - 7.0 mm
Height (H)	57.5 mm
Length (L)	58.1 mm
Min.Tensile Strength	445 N
Operating Temperature	-40 °C to +105 °C
Package Content	1000 pcs.
Package Content packed in	carton
Panel Thickness	0.6 - 6.0 mm
Panel Thickness max.	6.0 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	20.5 mm

