

## Technical data sheet

Article number:  
151-03549

**CMRCCHM10**

|                                  |                                                                           |
|----------------------------------|---------------------------------------------------------------------------|
| <b>Product Group</b>             | Heavy duty cable clamps                                                   |
| <b>Product Family</b>            | screwable, Inline Ratchet Clamps                                          |
| <b>Material</b>                  | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV) |
| <b>Colour</b>                    | Black (BK)                                                                |
|                                  |                                                                           |
| <b>Bundle Ø max.</b>             | 36.1 mm                                                                   |
| <b>Bundle Ø min.</b>             | 19.3 mm                                                                   |
| <b>CE Certification</b>          | No                                                                        |
| <b>Fixation Method</b>           | Screw Mount                                                               |
| <b>Flammability</b>              | UL 94 HB                                                                  |
| <b>for Hole Ø (FH)</b>           | 11.2 mm                                                                   |
| <b>Height (H)</b>                | 30.4 mm                                                                   |
| <b>Length (L)</b>                | 125.3 mm                                                                  |
| <b>Operating Temperature</b>     | -40 °C to +105 °C                                                         |
| <b>Package Content</b>           | 150 pcs.                                                                  |
| <b>Package Content packed in</b> | pack                                                                      |
| <b>ROHS compliant</b>            | Yes                                                                       |
| <b>UV-Stabilised</b>             | Yes                                                                       |
| <b>Width (W)</b>                 | 35.1 mm                                                                   |

HF ✓

RoHS ✓