

RF ASSEMBLY, RG_58_C/U, BNC (male), BNC (male), 50 Ohm, 1 GHz, 2000mm
30_BNC-1-200-21

Properties

- Standard RG cable
- Excellent RF performance for precision applications
- Suitable for use in application up to 1 GHz



Product configuration	
Type of cable	RG_58_C/U
Type description connector A	11_BNC-50-3-4/133_N
Series connector A	BNC, straight - plug
Type description connector B	11_BNC-50-3-4/133_N
Series connector B	BNC, straight - plug
Length	2000 mm
Length type	Cable length

Electrical data	
Impedance	50 Ω
Max. operating frequency	1 GHz

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22540506	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering information	
Item number	Item description
22540506	30 BNC -1-200-21/133 50 OHM

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P37954 / Date of publication: 02.06.2025 / uncontrolled copy