


ABRR044 ROUND ROCKER SWITCH 12/24VDC BLUE DOT LED ILLUMINATED

Specifications

Rating	12-24VDC
Lamp	BLUE DOT LED 12/24VDC
Switch action	ON-OFF, SPST, 3P, LED illumination
Maximum contact resistance	30MΩ
Minimum insulation resistance	500VDC 100MΩ
Withstand voltage	AC 1500V 1min
Electrical life & lamp life	10,000 cycles at full load
Operation force	300-600gf
Operating temperature	-25°C~+125°C

ABRR044



Features

- ROHS compliant
- Housing: Nylon #66 UL 94V-2
- Rocker: PC UL 94HB
- Illuminates at 12VDC & 24VDC
- Terminal material: Copper alloy AG plated
- Contact material: AgSnO₂In₂O₃ (10) / Cu
- LED lamp life - 10,000 hours