

40Vmax Magnetic Light XGT®, ML013G

1750 lx, 1200 lm

Model ML013G is a magnetic light powered by 40Vmax XGT Li-Ion battery.

This light can be used when performing maintenance work on construction machinery or heavy equipment, the light fixes with the magnet, allowing for hands free. It is easily attached in tight spaces. This work light is so compact and handy to hold with one hand. Features a foldable rotating LED head. Folds down to even more of a compact size.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Luminous flux	1200 / 800 / 500 Lumen
Illuminance	1750 / 1150 / 700 lx
Color temperature	5000 K
Continuous use XGT® 40Vmax / 2.0 Ah	6 / 9 / 13 h
Continuous use XGT® 40Vmax / 2.5 Ah	7,5 / 11 / 17 h
Continuous Use XGT® 40V Max / 4.0 Ah	12 / 18 / 29 h
Continuous use XGT® 40Vmax / 5.0 Ah	15 / 23 / 35 h
Product Dimensions (L x W x H):	196 x 91 x 284 mm
Dimensions, foldable (L x W x H)	196 x 91 x 161 mm
Angle range horizontal	300 °
Angle range vertical	180 °

User benefits

- Compact and lightweight for single handed operation
- Light diffusing lens softens LED light to reduce glare and provides widespread illumination
- 3 brightness settings (high / medium / low)
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery capacity warning function automatically notifies the user about reduction in battery capacity with the decrease of illuminance

EAN 0197050017529

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing