



TCP BULKHEAD WITH MOTION SENSOR

TCP IP65 Bulkhead Light with Microwave Sensor - This eco-friendly, IP65 LED light offers switchable wattage and variable CCT. Suitable for indoor/outdoor use, wall/ceiling mounted. Made with recycled materials.



Quick Install



Microwave Motion Sensor



Multi Wattage



IP65



CCT - Warm to Cool

Product Specifications

Bulkhead	Motion sensor
Emergency	No
Motion sensor	Microwave motion sensor
Colour temperature	3000K / 4000K / 6000K
Lumens	1100 - 1900 LM
Power	11 W / 15 W / 19 W
IP rating	IP65 / IK10
Lifetime	50,000 Hours
Dimmable	Dimmable via step switch
Beam angle	120°
CRI	80

Working temperature	-10° to 40°C
Mercury (Hg)	0 MG
Start up time	0 Seconds
Voltage / Frequency	220-240 V / 50/60Hz
Dimensions	W 300 x D 300 x H 75 MM
Product Code	TCPWHBULKTPBH300MW
Barcode	8720039609471