




TCP OUTDOOR FLOODLIGHT

Easy installation with a screwless terminal connector, made from recycled materials. IP65 rated for indoor/outdoor use, and has a tempered glass diffuser for enhanced durability.



Quick Install



IP65



Screwless Terminal



Mixed Recycle Materials

Product Specifications	TCPLIGHT10W3434	TCPLIGHT20W3340	TCPLIGHT30W3443	TCPLIGHT50W3446
PIR motion sensor	No	No	No	No
Lumens	1600 LM	3200 LM	4800 LM	8000 LM
Colour temperature	4000K	4000K	4000K	4000K
Power	10w	20w	30w	50w
IP rating	IP65 / IK10	IP65 / IK10	IP65 / IK10	IP65 / IK10
Lifetime	30,000 Hours	30,000 Hours	30,000 Hours	30,000 Hours
Dimmable	Non dimmable	Non dimmable	Non dimmable	Non dimmable
Beam angle	120°	120°	120°	120°
CRI	70	70	70	70
Energy rating	C	C	C	C
Voltage / Frequency	220-240 V / 50/60Hz	220-240 V / 50/60Hz	220-240 V / 50/60Hz	220-240 V / 50/60Hz
Dimensions	W 130 x D 58 x H 108 MM	W 130 x D 89 x H 170 MM	W 185 x D 58 x H 130 MM	W 218 x D 58 x H 209 MM
Barcode	8720039606623	8720039606678	8720039607316	8720039607606