




Solderless terminals

**LIPPED BLADE** Non-insulated

Certificate No.: E42024




Applicable Wire AWG#(mm ²)	Part No.	Standard	Dimensions mm (in.)										Tool No.				Qty/box
			B	L	G	E	G ₁	ø D	ø d ₁	T	W	X	YHT-2210	YA-1	YA-2	YA-4	
16 to 14 (1.04 to 2.63)	AH-2		4.6 (.181)	21.6 (.850)	16.8 (.661)	4.8 (.189)	13.0 (.512)	4.1 (.161)	2.3 (.091)	0.8 (.031)	2.0 (.079)	1.7 (.067)	0	0	0	0	1,000

Note:1) The part numbers indicated in the above table are for products with a brazed seam.

When ordering products with a butted seam, add the prefix "WS" to the part number (ex. AH-2 → **WSAH-2**).

2) Delivery lead times may vary depending on the product. Contact JST for details.

Solderless terminals

**LIPPED BLADE** vinyl-insulated

Certificate No.: E42024


Applicable Wire AWG#(mm²)	Part No.		Standard	Dimensions mm (in.)									Color	Tool No.						Qty/box
	Straight	Flared		B	L	G	ℓ	G ₁	ø D		T	X		YNT-2216	YNT-1614	YNT-1210S	YA-1	YA-2	YA-4	
									Str.	Fld.										
22 to 16 * (0.25 to 1.65)	—	FVAH-1.25		4.6 (.181)	25.8 (1.016)	16.8 (.661)	9.0 (.354)	13.0 (.512)	3.2 (.126)	4.0 (.157)	0.8 (.031)	1.7 (.067)	Red	0			0	0	0	500
16 to 14 (1.04 to 2.63)	—	FVAH-2		4.6 (.181)	25.8 (1.016)	16.8 (.661)	9.0 (.354)	13.0 (.512)	3.9 (.154)	4.5 (.177)	0.8 (.031)	1.7 (.067)	Blue		0		0	0	0	500
12 to 10 (2.63 to 6.64)	—	FVAH-5.5		4.6 (.181)	30.3 (1.193)	16.8 (.661)	13.5 (.531)	13.0 (.512)	5.4 (.213)	6.8 (.268)	0.8 (.031)	1.9 (.075)	Yellow			0			0	250

Note:1) The part numbers indicated in the above table are for products with a brazed seam.




When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FVAH-1.25 → **FVWSAH-1.25**).2) *The crimping will be more secure if the total cross-sectional area of the wire is at least 0.5 mm².Examples: If the cross-sectional area of the wire is 0.3 mm², fold the wire in two when crimping the terminal.If the cross-sectional area of the wire is 0.5 mm², crimp the terminal onto the wire as it is.

3) Delivery lead times may vary depending on the product. Contact JST for details.

Solderless terminals



LIPPED BLADE vinyl-insulated with copper sleeve



Certificate No.:  E42024

Applicable Wire AWG#(mm ²)	Part No.		Standard	Dimensions mm (in.)									Color	Tool No.						Qty/box
	Straight	Flared		B	L	G	ℓ	G ₁	Ø D		T	X		YNT-2216	YNT-1614	YNT-1210S	YA-1	YA-2	YA-4	
									Str.	Fld.										
22 to 16 (0.25 to 1.65)	VDAH-1.25	FVDAH-1.25		4.6 (.181)	26.4 (1.039)	16.8 (.661)	9.6 (.378)	13.0 (.512)	3.5 (.138)	4.0 (.157)	0.8 (.031)	1.7 (.067)	Red	0			0	0	0	500
16 to 14 (1.04 to 2.63)	VDAH-2	FVDAH-2		4.6 (.181)	26.4 (1.039)	16.8 (.661)	9.6 (.378)	13.0 (.512)	4.1 (.161)	4.7 (.185)	0.8 (.031)	1.7 (.067)	Blue		0		0	0	0	500
12 to 10 (2.63 to 6.64)	VDAH-5.5	FVDAH-5.5		4.6 (.181)	30.8 (1.213)	16.8 (.661)	14.0 (.551)	13.0 (.512)	5.7 (.224)	6.5 (.256)	1.0 (.039)	1.9 (.075)	Yellow			0			0	250

Note : 1) The part numbers indicated in the above table are for products with a brazed seam.
When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FVAH-1.25 -> **FVWSAH-1.25**).
2) Delivery lead times may vary depending on the product. Contact JST for details.