




024140200

Polyester Enclosure Standard

406 x 401 x 201 mm

Polyester Enclosure Standard 406 x 401 x 201 mm

[Catalogues](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)[Assignmentplan](#)[Terminal Mounting](#)

Technical data

Height	406 mm
Width	401 mm
Depth	201 mm
Material	Polyester
Colour	Squirrel Gray (RAL 7000)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-30 °C
temperature max.	90 °C
Seal material	CR-(Chloroprene)
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10 ¹² Ohm
Surface resistance norm	IEC 60093
Special colours on request	Yes
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	39269097
Weight	8.3 kg
GTIN	4250157900760


ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100111190
Mounting plate for 02.4140xx



100270010
HINGE EXTERNAL / GREY



100311020
Outer bracket fastening set M6



100614270
DIN rail 35/7,5 for xx.234011



100620110
Earth rail for 01.234011