




077001030

Tabletop Enclosure Wavetronic

324 x 268 x 147 mm

Tabletop Enclosure Wavetronic 324 x 268 x 147 mm

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)

Technical data

Height	147 mm
Width	268 mm
Depth	324 mm
Enclosure material	Halbschale: DIN EN 1706 EN AC-AISI 12 (Fe), Seitenprofile: DIN EN 573 EN AW-ALMgSi
Colour Electronic Enclosure	Powder coating, housing RAL 7035, light grey, base elements RAL 7024 graphite grey
Degree of protection norm	EN 60529
Impact strength	Other
temperature min.	-30 °C
temperature max.	80 °C
Other versions on request	EMV

Commercial data

Order unit	1 Piece
Customs tariff number	76169990
Weight	3.1 kg
GTIN	4250157903365


ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany


Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories




077000810

Mounting feet Wavetronic



077000820

Carrying handle Wavetronic



077000830

19 Plug-In Set Wavetronic



077000930

Frontplate Wavetronic 3 (Set, 2 pcs)



100360010

Spring nut-set 8 x M5