

Miniature Hexagon

Contact Configurations and Types	Shell Styles	Contact, Shell Materials and Latching Mechanisms	Ratings
<p>126 Series</p> <p>4, 5, 7 and 9 contacts.</p>	<p>Molded backshells. Rack and panel. Cable to cable. Cable to panel.</p>	<p>Stamped, gold-plated contacts. Locking clips. Lock-sleeve. Hood and cable clamp.</p>	<p>500 VAC (RMS) at sea level.</p>



126 Mini Hex

Military Audio Connectors

<p>U and GC Series</p> <p>5, 6 and 10 contacts. Solder. Crimp. Printed Circuit.</p>	<p>Plug. Receptacle.</p>	<p>Variety of contacts, including gold over nickel. Stainless steel, passivated. J slot twist lock mating.</p>	<p>MIL-C-55116 (QPL). MIL-C-10544.</p>
--	---	--	---



GC Audio Panel Mount

GC Audio Cable Mount



NOTE: Dust Caps Available: Cadmium plated, black anodized, aluminum and stainless steel.
 Rope, chain, bead and other cable fastener types.
 Rubber or neoprene gaskets.