



NFT-03C

Specifications

Dimensions	5 x 5 x 3 (mm)
SPL (0.3W/10CM)	74dB
Rated Voltage	3V
Operating Voltage	to 4V
Mean Current Consumption	90mA (max)
Rated Frequency	4000 Hz
Operating Temperature	030~ +70°C
Weight	0.3 Grams



