




TMX-05H

Specifications

Dimensions	Dia 25 x 12.5 (mm)
SPL (0.3W/10CM)	104 dB
Rated Voltage	5V
Operating Voltage	to 6V
Mean Current Consumption	80mA (max)
Rated Frequency	1500 Hz
Operating Temperature	040~ +85°C
Weight	9 Grams

TMX-05H N/L Square wave 5V 50%
Distance at 10cm



Grams

