



SCG-16B-LS

Specifications

SPL (0.3W/10CM)	92.5dB +/- 3dB
Nominal Input	0.3W (1.55Vrms)
Impedance	8 +/- 1.2Ω
Resonance Frequency	780 +/- 100Hz
Operating Temperature	030~ +70°C
Weight	1.2 Grams



