

---

Item no.: 243-308  
Product description: MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES;  
8-CONDUCTOR TERMINAL BLOCK; PUSH-WIRE  
CONNECTION

---



Packing unit 500 10\*50 pieces

pole count	8
Cross section from [AWG]	22 AWG
Cross section to [AWG]	87 AWG
Diameter from	0,6 mm
Diameter to	0,8 mm
Measured voltage EN	100 V
Measured shock voltage	1,5 kV
Pollution degree	2
Current intensity EN	6 A
Voltage CSA	150 V
Current CSA	7 A
Voltage UL	125 V
Current UL	7 A
Weight	1,44 g
Color	light grey
Wiring type	Side-entry
No. of connection Points	8
No. of potentials	1
Height	6,8 mm
Height	0,268 in
Width	18,4 mm
Width	0,725 in



Depth	0,394 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0,22 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
243-308	ABS	04-HG476172-PDA	100	6	0,5-0,75
243-308	CSA	18677-31	150	7	22-20mixed/(4x18)
243-308	CSM	017956	100	6	0,5-0,75
243-308	DEMKO	105047	100	6	4x0,5-1,0
243-308	KEMA	92.6146.01	100	6	0,6/0,8
243-308	LR	04/20013(E1)	100	6	0,5-0,75
243-308	RMR	11130002	100	6	0,5-0,75
243-308	RosTesT	B09523	100	6	0,5-0,75
243-308	SEMKO	9144043	100	6	0,33-0,52/4x0,82
243-308	UL	E45172	125	7	22-18
243-308	VDE	2574-1440-4031	100	6	4x0,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected