

## DB DIS-BOARD

**DB Dis-Board System.**

The Absolute, Original, Moulded Socket Strip.

From its humble origins as the first moulded multi socket unit, the Dis-Board Systems have been developed to meet the needs of very diverse industries and applications. In particular the development of information technology has led to a proliferation of workstations in all works of life. Portable Dis-Board are the ideal choice for tough environments such as workshops, factories and industrial plant, whilst other fixed variants are specified by major financial services companies and retail chains.

**System Benefits:**

- Utilises UK standard 86mm plate technology allowing the widest range of power and data accessories to be mounted, off-standards and international variants such as Schuko.
- Portable, trailing, workstation and 19" variants.
- Available with power lead and plug or just entry gland for on-site wiring.
- Impact resistant accessory plates and GRP base for strength and durability.

In addition to the standard ranges shown below, the concept has been adopted as a platform for custom made specials. For further details please contact [Aphel Sales Support](#).

**DB DIS-BOARD General Purpose Units**

**4 and 6 way white units offering unswitched or switched socket with optional filtering and circuit protection.**

**Portable with 2m Lead and Plug**

Sockets (n)	Unit Type	Ref.
4 way UK	Unswitched	DB4-001-0
4 way UK	Switched	DB4-011-0
6 way UK	Unswitched	DB6-001-0
6 way UK	Switched	DB6-011-0

**Portable with Filter, 2m Lead and Plug**

Sockets (n)	Unit Type	Ref.
4 way UK	Unswitched	DB4-001-1
4 way UK	Switched	DB4-011-1
6 way UK	Unswitched	DB6-001-1
6 way UK	Switched	DB6-011-1
<b>Portable with 2m Lead and Plug, and Onboard RCD</b>		
Sockets (n)	Unit Type	Ref.
4 way UK	Unswitched	DB4-001-2
4 way UK	Switched	DB4-011-2
<b>Portable with 2m Lead and RCD Plug</b>		
Sockets (n)	Unit Type	Ref.
4 way UK	Unswitched	DB4-001-3
4 way UK	Switched	DB4-011-3
6 way UK	Unswitched	DB6-001-3
6 way UK	Switched	DB6-011-3
<b>Fixed 20mm Conduit Entry</b>		
4 way UK	Unswitched	DB4-009-0
4 way UK	Switched	DB4-019-0
6 way UK	Unswitched	DB6-009-0
6 way UK	Switched	DB6-019-0
<b>Fixed 20mm Cable Gland Entry</b>		
4 way UK	Unswitched	DB4-000-0
4 way UK	Switched	DB4-010-0
6 way UK	Unswitched	DB6-000-0
6 way UK	Switched	DB6-010-0

### DB DISBOARD 19" Rack Units



2 U high units for mounting into 19" racking cabinets to BS5854 Available in all normal socket options as well as IEC 320 variants



<b>19" Horizontal with 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
5 way UK	Unswitched	DB5-001-0
5 way UK	Switched	DB5-011-0
5 way UK	Switched neon	DB5-081-0
<b>19" Horizontal with Filter, 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
5 way UK	Unswitched	DB5-001-1
5 way UK	Switched	DB5-011-1
<b>19" Horizontal IEC320 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.

6 way C13		DB5-091-0
8 way C13		DB5-101-0
10 way C13		DB5-121-0
20 way C13		DB5-021-0
<b>19" Horizontal IEC320 with 6.3A Fuse, 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
6 way C13	Single 6.3A fuse	DB5-131-0
8 way C13	Single 6.3A fuse	DB5-141-0
10 way C13	Single 6.3A fuse	DB5-031-0
<b>19" Horizontal IEC320 with Ind. 6.3A Fuses, 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
6 way C13	Individual 6.3A fuse	DB5-151-0
8 way C13	Individual 6.3A fuses	DB5-071-0
10 way C13	Individual 6.3A fuses	DB5-041-0
<b>19" Horizontal IEC320 with Filter, 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
6 way C13		DB5-091-1
8 way C13		DB5-101-1
10 way C13		DB5-161-1
<b>19" Horizontal IEC320 with Filter, 6.3A Fuse, 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
6 way C13	Single 6.3A fuse	DB5-131-1
8 way C13	Single 6.3A fuse	DB5-141-1
10 way C13	Single 6.3A fuse	DB5-171-1
<b>19" Horizontal IEC320 with Filter, Ind. 6.3A Fuses, 2m Lead and Plug</b>		
Sockets (n)	Unit Type	Ref.
6 way C13	Single 6.3A fuse	DB5-151-1
8 way C13	Single 6.3A fuse	DB5-071-1