

05.28.320

Hinged-Standoffs

Length	20,0 mm
Material	Brass
Plating	Nickel plated
Thread I-1/Innside / Length	M3 / 10,0 mm
Thread A-2/Outside / Length	M3 / 10,0 mm
Type	Hinged Standoffs
Model	Inside/Outside
Thread 1 Lenght	10,0 mm
Thread 2 Lenght	10,0 mm
Model	Booth Side Same
Special	□0043363103G.Teil M RoHS konform

