

05.28.321

Hinged-Standoffs

Length	21,0 mm
Material	Brass
Plating	Nickel plated
Thread I-1/Innside / Length	M3 / 6,0 mm
Thread A-2/Outside / Length	M3 / 15,0 mm
Type	Hinged Standoffs
Model	Inside/Outside
Thread 1 Lenght	6,0 mm
Thread 2 Lenght	15,0 mm
Model	Schenkel ungleich
Special	<input type="checkbox"/> 0043363153G.Teil M RoHS konform

