

05.52.013 **Round Spacer-Brass /
Wall Thickness 0,95 mm**

Length	1,0 mm
Material	Brass QQ-B-6261 ASTM-B-16
Plating	Nickel plated
Inside Diameter	for M2.5-Dia.2.5-2.7
Outside Diameter	4,5 mm
Model	Round Spacer
Type	Standard, Endsite Plain
Attribute	gedreht
Design	Cuttet
	RoHS konform

