









# 80-Series Cutters



## OVAL

### 8130-8162



Product code	EAN code 731415+	A mm inch	B mm inch	C mm inch	D mm inch	F mm inch	Capacity mm inch	Bevel		
8130	0050918	108.0 4.25	8.0 0.31	8.0 0.31	5.0 0.20	0.8 0.03	0.2 - 1.25 0.01 - 0.05	Micro	43	1
8131	0050925	108.0 4.25	8.0 0.31	8.0 0.31	5.0 0.20	0.8 0.03	0.1 - 1.25 0.01 - 0.05	Flush	43	1
8132	0050932	108.0 4.25	8.0 0.31	8.0 0.31	5.0 0.20	0.8 0.03	0.1 - 0.8 0.01 - 0.03	Ultra	44	1
8140	0050949	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.2 - 1.25 0.01 - 0.05	Micro	46	1
8141	0050987	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.1 - 1.25 0.01 - 0.05	Flush	45	1
8142	0051007	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.1 - 1.0 0.01 - 0.04	Ultra	46	1
8150	0051113	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.3 - 1.6 0.01 - 0.06	Micro	50	1
8150J	0051137	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.3 - 1.6 0.01 - 0.06	Micro	49	1
8151	0051199	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.2 - 1.6 0.01 - 0.06	Flush	49	1
8152	0052097	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.2 - 1.25 0.01 - 0.05	Ultra	49	1
8160	0051229	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.4 - 2.0 0.02 - 0.08	Micro	88	1
8160J	0051250	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.4 - 2.0 0.02 - 0.08	Micro	87	1
8161	0051328	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.3 - 2.0 0.01 - 0.08	Flush	88	1
8162	0051335	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.3 - 1.6 0.01 - 0.06	Ultra	88	1

Type "J" edges for stripping and cutting insulated copper wire.



If an 80-series cutter is desired with ESD-safe sleeves, then add the suffix CO or DS to the product code (Example: 8162 CO)