

05.54.103

**Round Spacer-Brass /
Wall Thickness 1,85 mm**

Length	10,0 mm
Material	Brass QQ-B-6261 ASTM-B-16
Plating	Nickel plated
Inside Diameter	for M4- Dia. 4.1-4.5
Outside Diameter	8,0 mm
Model	Round Spacer
Type	Standard, Endsite Plain
Attribute	gedreht
Design	Cuttet
	RoHS konform

