

GP Batteries

Data Sheet

Model No.: GP15AU

NO MERCURY ADDED

Description : Mercury & Cadmium Free Alkaline Manganese Battery, AA Size

Chemical System : Alkaline Manganese

Nominal Voltage : 1.5 Volts

Nominal Dimensions: Ø14.5 mm x 50.5 mm

Terminals : Protruded positive(+) and flat negative(-) contacts

Jacket : Foil jacket


Applications : All electronic devices, e.g. toys, digital camera, mobile phone, PDA, photographic equipment, data banks, calculators, audio appliances, remote controls, paging machines.

Warranty Period : 36 months

Average Weight : 23g

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
10 Ohms	24 Hrs/Day	0.9V	19.0Hrs



At 20±2°C within 30 days of manufacture

Cross References:

GP	JIS	IEC	Eveready	Duracell
15AU	LR6	LR6	E91	MX1500

