

## Min/Max Memory Alarm Thermometer



Min/Max Memory Alarm Thermometer

ST-9258

### Features:

- Measures in °C or °F
- Programmable alarm for min/max values
- Audible alarm at the high/low temperature limits
- 30mm LCD display with function indicators
- Min/max memory
- Data hold function retains displayed value
- Auto shut off after 1 hour
- Sampling rate of one reading per second
- 100mm x 4mm ø stainless steel pointed tip probe with handle and 1m cable
- Impact resistant ABS case incorporates a desk stand and compartment for the sensor cable when not in use
- Low battery indicator

### · Supplied with a probe protector cap & battery

### · Optional Calibration Certificate available

ACAL-ST Calibration Certificate - Issued at 4 points: 25°C, 50°C, 75°C & 100°C. (Additional points are available if required. These must be specified at the time of order. Please call for price and details.)

**For best results** ensure the thermometers probe tip is immersed at least 10mm into the substance being tested, as the sensor is located in the bottom 10mm of the probe

### AST-9258 Alarm Thermometer

#### Technical Specifications

Range	-50° to +150°C
Resolution	0.1°C (-19.9 to +150°C), 1° (others)
Accuracy	±1° (-30° to +150°C), ±2° (others)
Sampling	every one-second
Power	1 x 1.5V button cell battery
Dimensions	120 x 60 x 20mm
Weight	77g