

**Enclosure
KLIPPON K2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	0342100000
Part designation	KLIPPON K2
Version	Enclosures, 70 mm, 45 mm, 100 mm, Aluminium AISi12
GTIN (EAN)	4008190104641
Qty.	10 pc(s).

**Enclosure
KLIPPON K2**
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data
Dimensions (1)

Weight	280 g	Length	45 mm
Width	100 mm	Height	70 mm
Fixing dimension, width	88 mm		

General information

Fixing dimension, width	88 mm	Material	Aluminium AISi12
Surface	untreated	Cover fixing	M4 torx stainless steel screws with slot
Enclosure fixing	Holes 4 mm	Integral fixing	Threaded holes M3
Material	Aluminium AISi12	Resistance to shocks	10.00 J
Sealing material	Neoprene	Surface	untreated

Cable glands top/bottom

M 12	3	M 16	3
M20	2	Side of enclosure	left right

cable glands, left

M 12 (3)	1	M 16 (3)	1
----------	---	----------	---

cable glands, right

M 12 (2)	1	M 16 (2)	1
Side of enclosure	left right		

horizontal assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5	1x10
-----------------------------	------

vertical assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	*
---------------------------------	---

Approvals

Approvals institutes	CULUS; GERMLLOYD; GOSTEX; GOSTME25; MARITREG
----------------------	--

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------