




Marquardt GmbH  
Schloss-Str. 16  
78604 Rietheim-Weilheim

Germany


Phone  
: +49 (0) 7424 / 99-0  
Fax : +49 (0) 7424 / 99-2399

Net : [www.marquardt.de](http://www.marquardt.de)  
E-mail : [marquardt@marquardt.de](mailto:marquardt@marquardt.de)

## Product image / Drawings



## Technical data

<b>Product number</b>	<b>0133.0101</b>	
Actuator color / printing		
Business unit	Switches & Sensors	
Product family	Toggle switches	
Weight	24.960 g	
ROHS conform	yes	
Switching function	Changeover switch (DPDT)	
Material fixed contact	CuZn silver-plated	
Number of poles connections	2-polig Solder terminal	
Mechanical life endurance	5E4	
Rating IEC	2 A 250 V 1E4	
Actuators and additional actuators	lever: PA, black	
Housing description	base plate: Type 31, black bracket plate: CnZn nickel-plated threaded socket: CnZn nickel-plated, with knurled nut and hexagonal nut of nickel-plated CuZn	
Connection surface	bearing connection	silver plated
	external connection	silver plated
Contact material	CuZn silver plated	
Contact type	jump contact (roll contact)	
Miscellaneous	actuating torque 90.0 Nmm $\pm$ 27.0	
Type of fastening	central fastening M12 x 0.75	