














14/7 series made from plastic



- ▶ **Polypropylene**
resistant to most oils, acids and alkalis, noise absorbent on conveyors, withstands temperatures between -20° and +100° Celsius
- ▶ **Polyethylene**
resistant to most acids and alkalis, shock and impact resistant, absolutely harmless to foodstuffs, withstands temperatures between -40° and +80° Celsius
- ▶ **Robust and stable design**
- ▶ **Smooth internal walls**
for easy cleaning
- ▶ **Recessed handgrip on the back panel**
for secure manual transport
- ▶ **Flexible due to divider options**
- ▶ **Stacking lugs**
for secure stacking
- ▶ **Stackable**
with LF series, 14/6 series made from plastic and steel
- ▶ **Carrying bars can be purchased separately**

	Normal PE/PP	PPL 
Specific volume resistance	10 ¹⁸ Ohm x cm <	10³ Ohm x cm
Specific surface resistance	10 ¹⁴ Ohm	10⁴ Ohm

Semi-open front storage conductive plastic (PPL) – 14/7 series

Item	Interior dimensions when stacked L x W x useable height (mm)	Capacity (litre)	Unit	Order no.	Order no. 
 14/7-6 PP	63 x 91 x 43	0,26	50		--
14/7-6 PPL					6988
 14/7-6 M PP	63 x 44 x 43	0,26	50		--
with injected central partition					
14/7-6 M PPL					7008
 14/7-5 PP	133 x 88 x 66	0,8	50		--
14/7-5 PPL					6968
 14/7-4 PP	191 x 125 x 109	2,6	40		--
14/7-4 PPL					6928
 14/7-3 Z PP	291 x 182 x 132	7,2	28		--
14/7-3 Z PPL					6888
 14/7-3 ZD PP	292 x 430 x 129	17,0	10		--
with grooves for dividing wall ZW 3 ZD					
14/7-3 ZD PPL					7018
 14/7-3 PP	291 x 181 x 185	10,0	20		--
14/7-3 PPL					6848
 14/7-2 H PP	445 x 280 x 129	16,0	14		--
14/7-2 H PPL					6808
 14/7-2 PP	442 x 280 x 183	23,0	10		--
14/7-2 PPL					6758
 14/7-2 Z PP	442 x 280 x 285	37,0	1		--
14/7-2 Z PPL					6718
 14/7-1 PE	607 x 422 x 277	74,0	1		--
14/7-1 PPL					16358