

87

87 KNIPEX-"Cobra", the HiTech Water Pump Pliers

patented

DIN ISO 8976

87 01 150



87 01 180



87 01 250



87 01 300



87 02 250



87 05 250



- ▶ fast adjustment directly on the workpiece: fast and comfortable handling
- ▶ fine adjustment: ensures optimum adjustment to differently sized workpieces and user-friendly handle position;
 - 87 01 150: 11 adjustment positions
 - 87 01 180: 11 adjustment positions
 - 87 01 250: 11 adjustment positions
 - 87 01 300: 14 adjustment positions
 - 87 01 400: 27 adjustment positions
 - 87 01 560: 20 adjustment positions
- ▶ secure catching of the hinge bolt: no unintentional shifting
- ▶ box-joint design: high stability because of double guide
- ▶ self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- ▶ gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: low wear and secure gripping

KNIPEX special

KNIPEX-"Cobra" - the HiTech Water Pump Pliers. No more time-consuming test-adjusting of the correct opening size. Just position the upper jaw to the workpiece, push button and move close the lower jaw, ingeniously simple.

- ▶ one-hand adjustment
- ▶ guard prevents operators' fingers being pinched
- ▶ favourable lever action: optimum transmission of force
- ▶ Chrome Vanadium electric steel, oil-hardened and tempered

Model 87 01 150:

- ▶ Mini-"Cobra", length only 150 mm



Self-locking on pipes and nuts. No slipping on the workpiece and less handforce required



Fine adjustment by pushing a button: quick and comfortable



Fast and firm adjustment directly on the workpiece

Article-No.	EAN-Code	Head	Handles	Capacities		g
				for pipes	for nuts	
	Length Code			for pipes	for nuts	
	mm 4003773-			⌀ Inch	⌀ mm (across flats)	
87 01 150	060116	polished	with non-slip plastic coating	1 1/4	30	135
180	013297			1 1/4	30	170
250	013303			1 1/2	36	300
300	014157			2	46	545
400	005636	polished	plastic coated	3 1/2	95	1190
560	044321			4 1/2	120	2760
87 02 180	042396	polished	with two-colour	1 1/4	30	185
250	040316		dual component	1 1/2	36	320
300	029144		handles	2	46	580
87 03 180	005667	chrome plated	with non-slip plastic coating	1 1/4	30	170
250	005674			1 1/2	36	300
300	014119			2	46	545
87 05 250	005681	chrome plated	with two-colour	1 1/2	36	320
300	014126		dual component handles	2	46	580



Gripping surfaces with special hardened teeth for secure gripping of differently shaped workpieces

KNIPEX-"Cobra XL/XXL" see also page 73