

EasyView™ Light Meter with Memory

✓ **Store and recall up to 50 measurements**
With relative or real time clock stamp

Features:

- Wide measurement range to 99,990Fc (999,900Lux) with resolution of 0.001Fc and 0.01Lux
- Luminous intensity (candela) calculations
- Ripple function excludes the effect of stray light from the primary light source measurement
- Auto Power off with disable feature
- Multiple point average function
- Timed-Hold, Relative in absolute value or % deviation, and Comparator function with high low alarms
- Cosine and color corrected, CNS 5119 Class II
- Complete with built-in stand, light sensor and protective cover with 36" (0.9m) cable, protective holster, 6 AAA batteries, and carrying case



Wide range for taking measurements in direct sunlight

Ordering Information:

EA33.....EasyView™ Light Meter with Memory
EA33-NISTEA33 with NIST Certificate

Specifications	
Display Counts	999,999 count LCD
Fc Range	9.999Fc, 99.99Fc, 999.9Fc, 9,999Fc, 99,990Fc
Lux Range	99.99Lux, 999.9Lux, 9999Lux, 99,990Lux, 999,900Lux
Max. Resolution	0.001Fc/0.01Lux
Basic Accuracy	±3%
Cosine & Color Corrected:	Yes
Dimensions:	5.9 x 2.8 x 1.4" (150 x 72 x 33mm)
Weight:	11.29oz (320g)

