

Application:

With ammeters, wattmeters and cross current compensation.

Frequency:

50-400Hz

Insulation Level:




- 600 Volts, 10kV BIL full wave
- Flexible leads are UL 1015 105°C, CSA approved #16 AWG, 24" long
- Non-standard length to be specified
- Terminals are brass studs No. 8-32 UNC with one flat washer, lockwasher and regular nut
- SFT case styles also available as SFL with leads
- Approximate weight: 0.9 lb

Approvals



Model 76

Window Diameter 3.00"



Catalogue Number	Current Ratio	Accuracy at 60Hz	Burden VA at 60Hz
76**-201	200:5	± 1%	5.0
76**-251	250:5	± 1%	5.0
76**-301	300:5	± 1%	6.0
76**-401	400:5	± 1%	10.0
76**-501	500:5	± 1%	10.0
76**-601	600:5	± 1%	10.0
76**-751	750:5	± 1%	10.0
76**-801	800:5	± 1%	12.5
76**-102	1000:5	± 1%	12.5
76**-122	1200:5	± 1%	12.5
76**-152	1500:5	± 1%	12.5
76**-162	1600:5	± 1%	12.5
76**-202	2000:5	± 1%	15.0