


**SPECIFICATION
CONTROL DRAWING**
Crystal Resonator

FREQUENCY
307.200000kHz



Holder Style	HC51U
Mode	Fundamental
Adjustment Tolerance	± 50PPM at 25°C
Temperature Stability	± 100 PPM
Operating Temp. Range	-10°C to +60°C
Load Capacitance	30 pF
Marking	Mark AELX001L\FREQ+WWYY

Amdt Date	Change Note	AEL Code	
		X307K200L001	
		Issue Ref	A