

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643221039](#)
Status: **Active**
Overview: [cmc connectors](#)
Description: 0.635mm (.025") CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.5mm²

Documents:

3D Model	Product Specification PS-64319-001 (PDF)
Drawing (PDF)	Product Specification PS-64321-001 (PDF)
Product Specification PS-64318-001 (PDF)	RoHS Certificate of Compliance (PDF)



image - Reference only

General

Product Family	Crimp Terminals
Series	64322
Application	Power
Comments	* Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C. Current max = 6.0A for 0.635mm Terminal(0.75mm ² wire)
Crimp Quality Equipment	Yes
Overview	cmc connectors
Product Name	CMC, CP Terminal

Physical

Durability (mating cycles max)	20
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min - Mating	1.524µm (60µ"), 3.048µm (120µ")
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm-1.7mm
Wire Size AWG	N/A
Wire Size mm ²	0.5

Electrical

Current - Maximum per Contact	6A
Voltage - Maximum	250V AC

Material Info

Reference - Drawing Numbers

Application Specification	AS-64321-001
Packaging Specification	PK-98913-001
Product Specification	PS-64318-001, PS-64319-001, PS-64321-001
Sales Drawing	SD-64322-001

EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[64322Series](#)

Mates With

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#)

Use With

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#)