

Product Description



Application

- Sinusoidal slit ideal for protecting assembled cables or after assembly
- sinusoidal slit remains closed under torsion for the most part
- The STKP tool of the cable eater serves as an insertion tool
- Conduit holders for fastening (see table below)
- UV and weather resistant for photovoltaic applications

Technical Data

Approvals

GGVS, NFR-13-903 from 8.4 x 11.4

Note

Elongation at tear in accordance to DIN 53 455:
50-200% Impact resistance in accordance to DIN
53 453: without rupture Notched impact resistance
in accordance to DIN 53 453: without rupture
Flammability rating: UL 94 HB

Colour delivered

black, UV-resistant

Material

PA6 heat modified Cadmium free Halogen-free

Range of temperature

-40°C up to +140°C



Article List

Part number	Internal Ø x External Ø in mm	Suitable for holder SILVYN®	PU ring in m
SILVYN® RILL PA6 SINUS			
61806550	6,7 x 10	FCL 10 / 5550 6905	50
61806555	8,4 x 11,4		50
61806560	9,9 x 13	FCL 13 / 5550 6915	50
61806565	12,2 x 15,7	FCL 16 / 5550 6925	50
61806570	16,6 x 21,2	FCL 21 / 5550 6935	50
61806575	21,3 x 25,4	SPLIT COS 20 / 6180 6710	50
61806580	23,2 x 28,3	FCL 28 / 5550 6945	50