

Product Description

Enables the use of cable glands with larger connection threads than the existing threaded holes



Application range

- Machines
- Devices
- Housings

Benefits

- Enables the use of cable glands with larger connection threads than the existing threaded holes

Design

- Metric connection thread acc. to EN 50262



Technical Data

Material

Nickel-plated brass

Range of temperature

-60°C up to +200°C

Article List

Part number	Thread/ male M1	Thread/ female M2	Pieces / PU
SKINDICHT® ME-M			
52104450	12 x 1,5	16 x 1,5	100
52104452	16 x 1,5	20 x 1,5	100
52104454	20 x 1,5	25 x 1,5	100
52104456	25 x 1,5	32 x 1,5	50
52104458	32 x 1,5	40 x 1,5	50
52104460	40 x 1,5	50 x 1,5	25
52104462	50 x 1,5	63 x 1,5	25
SKINDICHT® ME-M hexagon			
52104463	63 x 1,5	75 x 1,5	25