

Universal Task Luminaire



SN 136

connected load
fitted with

work equipment
mains lead
luminaire body
material
tubular sections
material
surface
weight (net)
fastening

technology
usage
glare-free
balance of articulation joints
system of protection
class of protection
colour luminaire body
colour of tubular sections
article no.

230 V; 50 Hz

1 x compact fluorescent lamp TC-L 36 W
neutral white 4000 K
conventional ballast
approx. 1.5 m; shock-proof plug

plastic

steel tube
painted

approx. 3,7 kg

screw-down flange~table base (accessory)~table clamp
(accessory)~wall bracket (accessory)

switchable

switch

aluminiumised parabolic louvre

spring


IP 20

I


light grey

light grey

111011000



E_{min}: 217 lx
E_m: 933 lx
E_{max}: 2010 lx



measuring conditions: d=50cm

