

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Fast4
Catalogue number	2943
Date	06/03/2008

<p>Range Description 4 flute wood drill bits</p>	
<p>Features</p> <ul style="list-style-type: none"> • 4 flute configuration for fast waste removal • 100% more cutting blade than a flat bit or auger • Side blade for clean breakout • Nose screw pulls the bit through – less effort • Clean hole profile • Class leading cutting speeds • Fast change docking system (to 25mm) 	<div style="border: 1px solid black; height: 150px; width: 100%;"></div>

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T2943-16	4 Flute wood drill bit 16mm	5013969701821	82075090	10
T2943-20	4 Flute wood drill bit 20mm	5013969701838	82075090	10
T2943-22	4 Flute wood drill bit 22mm	5013969701845	82075090	10
T2943-25	4 Flute wood drill bit 25mm	5013969701852	82075090	10
T2943-32	4 Flute wood drill bit 32mm	5013969701869	82075090	10

Technical product information	<p>Recommended cutting speeds: 16 – 20mm between 1500 - 2000 RPM 22 – 25mm between 1000 – 1500 RPM 32mm between 800 – 1300 RPM</p> <p>Fast change docking system (6.4mm) hex shank provided on sizes up to 25mm Size 32mm has an 11mm hex drive shaft</p>
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE	This product range does not fall within the scope of RoHS or WEEE

compliance	regulations
Material safety data	None applicable
Warranty	C.K products are guaranteed for life against imperfect materials or workmanship Normal wear and tear of cutting edges and damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T2943-16	16	16	165	65	60	18	250	84
T2943-20	20	20	165	77	60	22	250	96
T2943-22	22	22	165	85	60	24	250	104
T2943-25	25	25	165	97	60	27	250	116
T2943-32	32	32	165	169	60	34	250	188

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T2943-16	145	290	100	978	24	10
T2943-20	145	290	100	1098	24	10
T2943-22	145	290	100	1178	24	10
T2943-25	145	290	100	1298	24	10
T2943-32	145	290	100	2018	24	10

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T2943-16	18	Blister	1	Card			138	Box
T2943-20	18	Blister	1	Card			138	Box
T2943-22	18	Blister	1	Card			138	Box
T2943-25	18	Blister	1	Card			138	Box
T2943-32	18	Blister	1	Card			138	Box