

Amphenol


Features:

- Microphone and Instrument Cables
- Heavy Duty screened cable
- Ultra flexible
- Solid pin male XLR's as standard

PRODUCT - FIGURE	DESCRIPTION	LENGTH _(Mtrs)	PART NUMBER
	Microphone Cable, (Balanced) XLR F / XLR M, Nickel Finish Connectors: AC3FJ AC3MMJ Cable: A	1	CA01-02-A-001
		3	CA01-02-A-003
		6	CA01-02-A-006
		9	CA01-02-A-009
		12	CA01-02-A-012
		15	CA01-02-A-015
		20	CA01-02-A-020
		30	CA01-02-A-030
	Instrument Cable, (Musician Series) 6.35mm/6.35mm, Straight/Right Angle, Satin finish, Gold Plated Contacts Connectors: ACPM-GN-AU ACPM-RN-AU CABLE: B	1	CA30-32-B-001
		3	CA30-32-B-003
		6	CA30-32-B-006
		9	CA30-32-B-009
		12	CA30-32-B-012
		15	CA30-32-B-015
		20	CA30-32-B-020
		30	CA30-32-B-030

STANDARD DATA

		VALUE	
GENERAL CHARACTERISTICS	Type	Microphone	Instrument
	Cable Code	A	B
	Number of Conductors	2	1
	Colour of Conductors	Blue and White	Natural
	Size of Conductors		
	AWG	N/A	20AWG
	Stranding	80/0.08mm	20/0.18mm
	Conductor Insulation		
	Material	PVC	PVC
	O.D	1.6mm +/- 0.01mm	1.7mm +/- 0.1mm
Strengthening Filler	Cotton	N/A	
Shield	Foil and Braid	Spiral	
Jacket			
Material	PVC (Black)	PVC (Black)	
O.D	6.8mm +/- 0.15mm	6.0mm +/- 0.15mm	
CLIMATIC CHARACTERISTICS	Operating Temperature	-30°C to + 70°C	