

datasheet for KUN 30 Au
article number: 931804703



product description:	order number: 931 804-703
description:	Shatter-proof, flexible, insulated coupling for a 4 mm diameter plug and solder connection up to a cable cross-section of 2.5 mm ² . Gold-plated brass socket.
typ:	KUN 30 gelb/yellow Au
system:	4 mm system
order number:	931 804-703
color	
other color versions:	
technical data	
type of contact:	unsprung socket
type of termination:	solder
rated voltage:	DC 60 V
rated current:	16 A
contact resistance:	2 mOhm
material	
contact material:	brass
contact surface material:	gold
housing material:	PVC-P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	