



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/20/2020	MBLACKWOOD



.36±.01
[9.2±0.2]

HIGH SPEED HDMI® CABLE WITH ETHERNET
5 TWISTED PAIR, INDIVIDUALLY SHIELDED
32AWG BARE COPPER
4 CONDUCTOR 32AWG BARE COPPER.
WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE
PLUS COPPER BRAIDED SHIELD
JACKET: PVC, BLACK O.D.: .177" [4.5]



PIN ASSIGNMENT



MODEL NO.	LENGTH(mm)	INCHES
VHA00022-1F	305±30	12.0±1.18
VHA00022-3F	915±30	36.0±1.18
VHA00022-6F	1830±30	72.0±1.18
VHA00022-10F	3050±30	120.0±1.18

NOTES:

- ELECTRICAL TEST:
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CONTACT RESISTANCE: 5 OHM MAX
 - INSULATION RESISTANCE: 5M OHM MIN
 - HI-POT TEST: DC 300V/10ms
 - PASS 4K@60Hz TEST
- PACKAGING:
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED INTO A CLEAR POLYBAG, LABEL PER LSP-010.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY MVEERAPPAN CHECKED BY DFRISIELLO APPROVED BY MBLACKWOOD	10/20/2020 10/20/2020 10/20/2020	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION SuperThin High Speed HDMI Cable with Ethernet, M/M SIZE A CAGE CODE 43321 ITEM NO. VHA00022 REV. A SCALE: NONE CAD FILE: VHA00022.SLDDRW SHEET 1 OF 1